

PRODUCT CONFIGURATIONS



V-1036

Sanitary Bulk Bag Discharger



USA

FLEXICON CORPORATION
2400 Emrick Boulevard
Bethlehem, PA 18020-8006
USA
Tel: 1 888 FLEXICON
(1 888 353 9426)
Tel: 1 610 814 2400
Fax: 1 610 814 0600
E-mail: sales@flexicon.com
Web: www.flexicon.com

CHILE

FLEXICON CHILE LIMITADA
Avenida Andres Bello # 1051
Oficina # 1602
Providencia
SANTIAGO
CHILE
Tel: +56 2 2415 1286
Fax: +56 2 2415 1393
E-mail: ventas@flexicon.com
Web: www.flexicon.com

UK

FLEXICON EUROPE Ltd.
182 John Wilson Business Park
Harvey Drive
Whitstable
Kent CT5 3RB
UNITED KINGDOM
Tel: +44 (0)1227 374710
Fax: +44 (0)1227 365821
E-mail: sales@flexicon.co.uk
Web: www.flexicon.co.uk

AUSTRALIA (BRISBANE)

FLEXICON CORPORATION
(AUSTRALIA) PTY LIMITED
78 Westgate Street
Wacol, QLD 4076
AUSTRALIA
Tel: +61 (0)7 3879 4180
Fax: +61 (0)7 3879 4183
E-mail: sales@flexicon.com.au
Web: www.flexicon.com.au

AUSTRALIA (SYDNEY)

FLEXICON CORPORATION
(AUSTRALIA) PTY LIMITED
Suite 5, Level 3
45-47 Hunter St.
Hornsby, NSW 2077
AUSTRALIA
Tel: +61 (0)7 3879 4180
Fax: +61 (0)2 9477 5548
E-mail: sales@flexicon.com.au
Web: www.flexicon.com.au

SOUTH AFRICA

FLEXICON AFRICA (PTY) LTD.
PO Box 10450
Linton Grange
Port Elizabeth 6015
SOUTH AFRICA
Tel: +27 (0)41 453 1871
Fax: +27 (0)41 453 1670
E-mail: sales@flexicon.co.za
Web: www.flexicon.co.za

flexicon[®]

Sanitary Bulk Bag Discharger

Flexicon's Sanitary Bulk Bag Unloading System eliminates dust during untying, discharging, retying, collapse and removal of bags while allowing thorough wash down.

The unloader, model BFC-F-X, is equipped with a patented SPOUT-LOCK® clamp ring* that forms a dust-tight connection between the clean side of the bag spout and the clean side of the equipment. The airtight system is vented to an integral dust collector that vacuums displaced air and dust, and collapses empty bags dust-free.

A patented, USDA-accepted POWER-CINCHER® flow control valve* cinches the bag spout concentrically, allowing dust-free retying of partially empty bags.

Promoting complete discharge of free- and non-free-flowing material from the bulk bag are FLOW-FLEXER® bag activators that raise and lower opposite bottom sides of the bag into a steep "V" shape, and a TELE-TUBE® telescoping tube that maintains constant downward tension on the bag as it empties and elongates.

All stainless steel construction with continuous ground and polished welds meets food, dairy and pharmaceutical standards, and allows rapid, thorough wash down.

A cantilevered I-beam with electric hoist and trolley allows raising and positioning of bulk bags without the aid of a forklift. Also offered is a BFF-F-X model equipped with top-mounted receiving cups and a removable bag-lifting frame for forklift loading of bulk bags.

The unit is available with a hopper and flexible screw conveyor that meet 3-A sanitary standards (shown) or a rotary airlock valve to feed material into a pneumatic conveyor line. It is also offered with an integral bulk bag conditioner to loosen materials that have solidified in the bag, and integrated scale systems for loss-of-weight batching directly from bulk bags.

**Patent(s) granted and/or pending.*

